


FILTER MEDIA DESIGNED TO FIT TSI RESPICON™

<u>MCE</u>	Mixed Ester		
5.0µm	M-5037X3500	100/pk	
<u>PVC</u>	Polyvinyl Chloride		
5.0µm	P-5037X3500	100/pk	
<u>PC</u>	Polycarbonate		
2.0µm	PC-2037X3500	100/pk	
<u>PTFE</u>	Teflon		
2.0µm	LZ02037X3550	50/pk	
5.0µm	L-5037X3550	50/pk	
<u>QUARTZ</u>			
0.3µm	QZ0337X3500	100/pk	
0.3µm	QZ0337X3500HT	50/pk	
	<small>Preheated for diesel exhaust analysis</small>		
<u>FIBER GLASS</u>			
0.3µm	FG0337X3500	100/pk	

Filter Format



Not To scale

All of the above materials are also available in a plain 37mm format without a center hole, to be used in the final stage of the Respicon™.

MCE	M-503700	100/pk	Quartz	QZ033700	100/pk
				QZ033700BK	100/pk
PVC	P-503700	100/pk		<small>For Diesel exhaust</small>	
PC	PC-203700	100/pk	Fiber Glass	FG03370F	500/pk
PTFE	LZ0203750	50/pk			
	L-503700	100/pk			